

Standard Features

- Electronically controlled load (ECL) self-diagnostic before internal repeatability test without an external weight in less than 1.5 minutes
- Internal calibration weight
- Impact shock detection
- Flow rate display
- RS-232 interface for connecting to printer or PC
- Password protection and anti-theft security slot
- GLP/GMP/ISO compliant to either AD-8127 printer or computer
- Transmits date, time, ID number, serial number, model, manufacturer and calibration data
- Rechargeable battery option for portability
- Super Hybrid Sensor Technology (SHS)
- Reverse backlit LCD display
- Optional glass breeze break
- Underhook weighing

Specifications

Weighing Units:

Gram, Ounce, Pound, Carat, Pennyweight, Troy Ounce, Grain (See technical manual for complete listing)

Operating Modes:

Animal Weighing, Comparator Function, ACAI Counting Function, Percentage, Density Determination, Statistical Calculation

Power:

120 V AC adapter, Approx. 30 VA

Stabilization Time:

GX-124A: Approx. 1.5 seconds
 GX-124AE: Approx. 2 seconds
 GX-224A, GX-224AE: Approx. 1 second
 GX-324A, GX-324AE: Approx. 2 seconds

Display Refresh Rate:

5 times/second, 10 times/second, 20 times/second

Calibration Weight:

GX-124A, GX-124AE: 100g
 GX-224A, GX-224AE, GX-324A, GX-324AE: 200g

Ionizer (fanless):

AE versions come standard with built-in fanless ionizer with external touchless sensor

Operating Temperature:

41 °F to 104 °F (5 °C to 40 °C) RH less than 85% (no condensation)

Est. Weight:

18 lb (8 kg)

Warranty:

Five-year limited

Return Policy:

A&D Weighing standard policy - restock fee may apply

| Model | Capacity | Readability | Repeatability | Linearity | Weighing Chamber | Pan Size | Dimensions | Part # | List Price |
|----------|----------|-------------|--------------------------------------|-----------|-------------------------|----------|-------------------------------------------------------------------------------------------|--------|------------|
| GX-124A | 120 g | 0.0001 g | 0.0001 g | ±0.0002 g | 8.78 in H (223 mm H) | Ø90 mm | 10.2 × 14.1 × 13.1 in (259 × 358 × 332 mm) <i>Includes Large Glass Breeze Break</i> | 200330 | Consult |
| GX-124AE | 120 g | 0.0001 g | 0.0001 g | ±0.0002 g | 8.78 in H (223 mm H) | Ø90 mm | 259 × 358 × 332 mm (10.2 × 14.1 × 13.1 in) <i>Includes Large Glass Breeze Break</i> | 200334 | Consult |
| GX-224A | 220 g | 0.0001 g | 0.0001 g | ±0.0002 g | 8.78 in H (223 mm H) | Ø90 mm | 259 × 358 × 332 mm (10.2 × 14.1 × 13.1 in) <i>Includes Large Glass Breeze Break</i> | 200332 | Consult |
| GX-224AE | 220 g | 0.0001 g | 0.0001 g | ±0.0002 g | 8.78 in H (223 mm H) | Ø90 mm | 259 × 358 × 332 mm (10.2 × 14.1 × 13.1 in) <i>Includes Large Glass Breeze Break</i> | 200335 | Consult |
| GX-324A | 320 g | 0.0001 g | 0.0002 g (300 g) 0.0001 g (200 g) | ±0.0003 g | 8.78 in H (223 mm H) | Ø90 mm | 259 × 358 × 332 mm (10.2 × 14.1 × 13.1 in) <i>Includes Large Glass Breeze Break</i> | 200333 | Consult |
| GX-324AE | 320 g | 0.0001 g | 0.0002 g (300 g) 0.0001 g (200 g) | ±0.0003 g | 8.78 in H (223 mm H) | Ø90 mm | 259 × 358 × 332 mm (10.2 × 14.1 × 13.1 in) <i>Includes Large Glass Breeze Break</i> | 200336 | Consult |

Options/Accessories

| Part# | A&D Model # | Description | Price |
|--------|--------------|--------------------------------------------------------------|---------|
| 192662 | GXA-03 | RS-232C Interface (D-sub 9-pin male) | Consult |
| 192663 | GXA-04 | Comparator output (requires 192667) | Consult |
| 192667 | AX-K05692 | MiniDIN 8-pin male for GXA-04 | Consult |
| 192671 | GXA-06 | Analog output (includes 192673) | Consult |
| 192674 | GXA-09 | Internal rechargeable battery (must be factory installed) | Consult |
| 192675 | GXA-10 | Large glass breeze break | Consult |
| 192676 | GXA-12 | Animal weighing pan (for models of 320 g capacity or higher) | Consult |
| 192677 | GXA-13 | Density determination kit (for 1 mg models only) | Consult |
| 192679 | GXA-23-PRINT | External key input interface for SW:137-PRINT foot switch | Consult |
| 192680 | GXA-23-RZERO | External key input interface for SW:137-REZERo foot switch | Consult |
| 192681 | GXA-23-PLUG | External key input interface for AX-T-314A-S plug | Consult |
| 192682 | GXA-24 | USB host interface (USB A type) | Consult |
| 192683 | GXA-25 | External fanless ionizer (static eliminator) | Consult |
| 192684 | GXA-26 | External IR switch (MiniDIN 4-pin male) | Consult |

